



SCHRÖDER

**IMAX 600/900 P**



Poultry injectors

# Versatile and robust for a wide range of poultry applications.



IMAX 600P

## Poultry injectors IMAX 600/900P

The IMAX 600/900P is the industry's most versatile injector designed specifically for chicken marination. It is a superior injector, with versatility to match. From bone-in to boneless, from whole birds to parts, the IMAX 600/900P Chicken Injector has every feature you'll need to process all of your chicken marination applications.

### DYNAMIC STRIPPER PLATE


Five positions for maximum flexibility: high setting for whole birds; low setting for pieces and parts.

### NEEDLE MANIFOLD

Pneumatic retraction for each individual needle, constant adjustable air pressure.

### PANEL CONTROL

Intuitive operation and ergonomically arranged.



### PRODUCT FEED

Two belt options available – standard features  
FM flat belt with optional CU flighted belt (600P) for cut-up operation.

### PUMP UNIT

Variable speed for optimum pressure control. Complete draining at the lowest point..

### FILTRATION

Four-stage filter eliminates clogged needles and pressure drops, resulting in higher yields and a more consistent product.

### TECHNISCHE DATEN – IMAX 600P

BELT WIDTH	620mm
NEEDLES	Single head with 343 or 540 needles, 3mm
PRODUCT STRIPPER	Five preset positions manually adjustable
PRODUCT INFEEED HEIGHT ADJUSTMENT MAX.	60 – 120mm
PRODUCT ADVANCE – FM FLAT BELT	45 / 90 / 180
PRODUCT ADVANCE – CU FLIGHTED BELT	On request.
MAXIMUM BONE HEIGHT – NEEDLE RETRACTION	165mm
SPEED	15 – 45 strokes/min
BRINE TANK	FT200

### TECHNISCHE DATEN – IMAX 900P

BELT WIDTH	920mm
NEEDLES	Single head with 511 needles, 3mm
PRODUCT STRIPPER	Five preset positions manually adjustable
PRODUCT INFEEED HEIGHT ADJUSTMENT MAX.	60 – 120mm
PRODUCT ADVANCE – FM FLAT BELT	45 / 90 / 180
PRODUCT ADVANCE – CU FLIGHTED BELT	On request.
MAXIMUM BONE HEIGHT – NEEDLE RETRACTION	120mm
SPEED	14 – 45 strokes/min
BRINE TANK	FT200

# IMAX technology

## Setting a whole new standard in chicken marination

The IMAX 600/900P Chicken Injector is specifically designed for all types of chicken marination applications and can handle chicken products varying from whole bone in birds to parts and bone-in and boneless cuts. Like all IMAX injectors, the IMAX 600/900P offers unparalleled injection distribution, consistency, and reliability. And since the 600/900P has been optimized for chicken marination, you will process a higher quality product with increased yields and the highest levels of production.

## A higher level of versatility.


When we set out to develop the IMAX 600/900P, we looked at chicken marination applications around the world. We combined that information with comprehensive research from leading European Universities specializing in applied fluid technologies. No detail was too small, no potential benefit was overlooked, and no compromises were made. The result is a highly flexible injector capable of processing a complete range of chicken products – a solution that provides processors with the opportunity to easily expand their production line.

## Greater performance.

Every component in the IMAX 600/900P has been optimized for chicken marination. Its dynamic stripper plate features two positions – a high setting for whole birds, and a low setting for parts and pieces. The lower area offers four settings each of 13 mm for fine tuning. A new, research-driven manifold design delivers a uniform brine flow to all needles with a consistent needle-tip pressure and injection rate.


## A superior design for food safety.

Like all IMAX injectors, the stainless steel 600/900P continues to lead the way in food safety. Its external brine filtration tank is easily accessible and can be quickly removed for cleaning and inspection to ensure products are not cross-contaminated. The ability to easily remove needles is another important part of food safety. The IMAX 600/900P has been designed so that all needles can be removed in less than 5 minutes.



### Control Panel

Recipe driven controls quickly recall programs for different product codes, allowing optimum performance and product consistency



### Brine feed

A superior, sanitary manifold design delivers uniform brine flow to the entry port of every needle.



### Dynamic Stripper Plate

- Five height positions to provide maximum flexibility. High setting for whole birds, low settings for cuts such as wings, fillets, leg quarters, tenders etc.
- Can be quickly configured between high and low setting
- Low setting provides four quick-change positions for optimum performance

# IMAX technology

## System features


The IMAX 600/900P Injector offers various optional system features which have been developed based on decades of experience. They include, for example, mechanical and electrical product detection, conductivity measurements (monitors the quality of the brine), brine level regulation, cleaning carriage and poultry guide rails on.

## Loading

The IMAX 600/900P comes standard with a conventional FM flat belt which is fed manually or by conveyor. The 600P is also available for chicken cut-up-line processes executed with a CU flighted belt with a specially designed hopper loader which automatically feed the 600P directly from a cut-up-line. The 600P injector can be easily changed from an FM to CU configuration, providing flexibility if the application changes in the future.

## Filtration

Filtration is important to achieving continuous and consistent performance. The solution to prevent clogged needles and an increase in pump pressure is maintaining the brine quality. Our standard system features four stages of filtration and can be optimally adapted to individual requirements. Rotary, circulation, suction and inline filters with a variety of different configurations guarantees an optimal filtration result. The individual filter elements have a straight-forward layout, are easy to access for the user, and simple to clean.



### Needle removal

An important part of food safety, the IMAX 600/900P has been designed for quick and easy needle removal – all needles can be removed in less than 5 minutes.



### Fine filter

Efficient filtering of small particles.

### Cut-up-line batch portioner

For batchwise loading of chicken parts.

## JBT PROTEIN PROCESSING

### SECONDARY

BRINE PREPARATION | HOMOGENIZATION | INJECTION  
INJECTION & RETURN MILLING | MACERATION | MASSAGING | TENDERIZATION  
TVI MEAT SLICING | -RAY TECHNOLOGY | AUTOMATED TRAY LOADING

### FURTHER

WEIGHING | PORTIONING/TRIMMING | COATING | FRYING & FILTRATION | PROOFING  
COOKING | COOLING | CHILLING | FREEZING | REFRIGERATION | CLIPPING & PACKAGING  
SOLUTIONS | X-RAY TECHNOLOGY | HIGH-PRESSURE PROCESSING (HPP)



Northfield

SCHRÖDER

STEIN

TIPPERTIE

Wolf-tec POLAR

XVISION

### North America

JBT  
1622 First Street  
Sandusky, OH 44870  
USA  
Phone +1 419 626 0304  
Fax +1 419 626 9560  
process-solutions@jbt.com

### Australia

John Bean Technologies Ltd.  
Cnr Marple Ave & Biloela Street  
Willawood New South Wales 2163  
Australia  
Phone +61 2 9723 2000  
Fax +61 2 9723 2085  
Natale.Greco@jbt.com

### Europe

Schröder  
Maschinenbau GmbH & Co. KG  
Esch 11  
33824 Werther  
Germany  
Phone +49 5203 9700 0  
info@schroeder-maschinen.de

### Latin America

John Bean Technologies  
Máq. Equip. Ind. Ltda.  
Av. Eng. Camilo Dinucci 4605  
14808-900 Araraquara  
São Paulo, Brazil  
Phone +55 16 3301 2000  
latinamerica.info@jbt.com

### Asia

John Bean Technologies (Thailand) Ltd.  
159/26 Serm-Mit Tower, Room No. 1602-3  
Sukhumvit 21 Road  
Klongtoey Nua Sub-district, Wattana District  
Bangkok 10110 Thailand  
Phone: + 66 2 257 4000  
Fax: + 66 2 261 4099  
infoasia-jbtfoodtech@jbt.com



We're with you, right down the line.™

[jbt.com/foodtech.com](http://jbt.com/foodtech.com)